



Technical sheet

No.

11FA05A

Issue

V01.0

Product family: Cable-ties - Nylon cable-ties
Item code: BR1576, BR2076, BR3076
Description: NYLON CABLE-TIES · REUSABLE

Image



Specifications

MATERIAL: polyamide (PA 6.6)
COLOR: natural
INSULATION SELF-EXTINGUISHING: UL 94 V2
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 1 (EN), type 21 (UL)
ASSEMBLY: open the package just before use

Code	Width (mm)	Length (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
BR1576	7,6	150	40	10	230	100/1000
BR2076	7,6	200	55	10	230	100/500
BR3076	7,6	300	82	10	230	



file n° E 223175

**HALOGEN
FREE**