



Technical sheet

No.

11FA09A

Issue

V01.0

Product family: Cable-ties - Nylon cable-ties UV resistant
Item code: N2412, N4912, N7412, N8912, N1012
Description: UV-RESISTANT NYLON CABLE-TIES · FOR HEAVY LOADS

Image



Specifications

MATERIAL: polyamide (PA 6.6) + carbon black
COLOR: black
OPERATING TEMPERATURE: from -40 °C to +85 °C
MINIMUM INSTALLATION TEMPERATURE: -10 °C
CHEMICAL RESISTANCE: good resistance to bases, oils, grease, chloride solvents. Limited resistance to acids. Not resistant to phenols.
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 1 (EN), type 21 (UL)
ASSEMBLY: open the package just before use

Code	Width (mm)	Length (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
N2412	12,4	230	57	9	1200	
N4912	12,4	480	136,5	9	1200	
N7412	12,4	730	216,1	9	1200	100/100
N8912	12,4	880	263,9	9	1200	
N1012	12,4	1000	305	9	1200	



file n° E 223175

**HALOGEN
FREE**

**UV
RESISTANT**