



Technical sheet

No. **11FC01A**

Issue **V01.1**

Product family: Cable-ties - Stainless steel cable-ties
Item code: S1345, S2045, S3045, S3745, S5245, S6845, S8445, S2079, S3079, S3779, S5079, S6879, S8479, S1079
Description: STAINLESS STEEL CABLE-TIES · SELF-LOCKING

Image



Specifications

MATERIAL: AISI 304 stainless steel
THICKNESS: 0,25 ± 0,05 mm
INSULATION SELF-EXTINGUISHING: not flammable
LOCKING MECHANISM: ball
OPERATING TEMPERATURE: from -60 °C to +300 °C
MINIMUM INSTALLATION TEMPERATURE: -60 °C
PLENUM RATING: AH-1
UV RAYS RESISTANCE: excellent
CHEMICAL RESISTANCE: excellent
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 2 (EN), type 2 (UL)

Code	Width (mm)	Length (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
S1345	4,6	125	38	15	890	100/100
S2045	4,6	200	61,9	15	890	
S3045	4,6	290	90,6	15	890	
S3745	4,6	360	112,8	15	890	
S5245	4,6	520	163,8	15	890	
S6845	4,6	680	214,8	15	890	
S8445	4,6	840	265,7	15	890	100/100
S2079	7,9	200	61,9	15	1500	
S3079	7,9	300	90,6	15	1500	
S3779	7,9	360	112,8	15	1500	
S5079	7,9	520	163,8	15	1500	
S6879	7,9	680	214,8	15	1500	
S8479	7,9	840	265,7	15	1500	100/100
S1079	7,9	1010	319	15	1500	



file n° E 223175