



Technical sheet

No.

11FC01B

Issue

V01.1

Product family: Cable-ties - Stainless steel cable-ties
Item code: SC1345, SC2045, SC3045, SC3745, SC5245, SC6845, SC8445, SC2079, SC3079, SC3779, SC5079, SC6879, SC8479
Description: STAINLESS STEEL CABLE-TIES · SELF-LOCKING · WITH POLYESTER COATING

Image



Specifications

MATERIAL: AISI 304 stainless steel
THICKNESS: 0,35 ± 0,05 mm
COLOR: black
INSULATION SELF-EXTINGUISHING: not flammable
COATING: polyester
LOCKING MECHANISM: ball
OPERATING TEMPERATURE: from -40 °C to +150 °C
MINIMUM INSTALLATION TEMPERATURE: -40 °C
PLENUM RATING: AH-1
UV RAYS RESISTANCE: excellent
CHEMICAL RESISTANCE: excellent
ACCORDING TO STD.: EN 62275:2015-02
CLASSIFICATION: type 2 (EN), type 2 (UL)

Code	Width (mm)	Length (mm)	Max bundle Ø (mm)	Min bundle Ø (mm)	Tensile minimum resistance (N)	
SC1345	4,6	125	38	15	450	100/100
SC2045	4,6	200	61,9	15	450	
SC3045	4,6	290	90,6	15	450	
SC3745	4,6	360	112,8	15	450	
SC5245	4,6	520	163,8	15	450	
SC6845	4,6	680	214,8	15	450	
SC8445	4,6	840	265,7	15	450	100/100
SC2079	7,9	200	61,9	15	800	
SC3079	7,9	290	90,6	15	800	
SC3779	7,9	360	112,8	15	800	
SC5079	7,9	520	163,8	15	800	
SC6879	7,9	680	214,8	15	800	
SC8479	7,9	840	265,7	15	800	



file n° E 223175

**HALOGEN
FREE**