

Premium VGA cable, 1.5 m

CCB-PPVGA-1.5M

- Dual shielded
- Ferrite cores
- Supports 1920x1080 resolution at 60Hz



Features

- VGA monitor HD15M/HD15M cable
- Premium quality dual-shielded (braiding & foil) with ferrite core
- Supports display resolutions up to 1080P FHD @ 60Hz

Specifications

Interface: VGA
Connectors: HD15 (male)
Supported resolutions: max. 1920x1080 @ 60 Hz
Shielding: braiding + foil
Ferrite filter: 2x
Fixation screws: yes

Packaging

Q'ty in crtn, pcs	50
Crtn volume, CUM	0.07
Crtn weight, kgs	11.54
Individual package size LxWxH:	145x145x45 mm
Carton size LxWxH:	767x332x275 mm
Country of origin	CN
Barcode	8716309121170
Customs code	8544429090

Certificates

