


Technical data sheet

Multifunctional connector 60

Item no. 6225710



Multifunctional connector for joining cable ladders with a side height of 60 mm. Symmetrical and asymmetrical reductions, infinitely-adjustable bends between 0–60° and add-on tees can be created.




St	Steel
FS	Strip galvanised

Master data

Item no.	6225710
Type	LMFV 620 FS
Description 1	Multifunctional connector
Description 2	for cable ladder
Dimension	60x200
Material	Steel
Material symbol	St
Surface	Strip galvanised
Surface to DIN	DIN EN 10346
Surface symbol	FS
Smallest sales unit (VG)	1,00 Piece
Weight	123,20 kg/100 pc.

Technical data



Length	604,00 mm
Width	200,00 mm
Height	60,00 mm
Side height	60,00 mm
Dimension B	200,00 mm
Version	Straight and angle connector
Plate thickness	1,50 mm
Suitable for cable support system width	200,00 - 200,00 mm
Suitable for cable tray system height	60,00 mm
Suitable for cable tray	☐
Suitable for mesh cable tray	☐
Suitable for cable ladder	☒
Suitable for maintaining electrical function	☐
Adjustable connector, horizontal	☒

Technical data sheet

Multifunctional connector 60

Item no. 6225710



Technical data

Adjustable connector, vertical	☐
Rustproof steel, pickled	☐
Connection type	Screw connector