

## GARDEN HOSE - PREMIUM

99612

### FUNCTIONS

- ☐ Double durability 4-layer flexible PVC hose with additives improving lowtemperature flexibility, resistant to bending and twisting
- ☐ Working pressure 10 bar
- ☐ Burst pressure of 30 bar
- ☐ Temperature range -25°C to +60°C
- ☐ Cadmium, barium, lead, and phthalate free



### TECHNICAL DATA

Product Code