

UB186-N

Art.-No.: 151-00782

HellermannTyton

2022-08-14



<https://www.hellermanntyton.com/151-00782>

Base Data

Colour	Natural (NA)
Fixation Method	Screw Mounting and Rivet
Material	Polyamide 6.6 (PA66)
Pack Cont.	100 pcs.
Package Content packed in	bag
PART DESCRIPTION	UB186-N-PA66-NA
Short Description	Screw Fixing Mount 18x12 mm natural

Product Dimensions

for Hole Ø (FH)	4.5 mm
Height (H)	9.0 mm
Length (L)	18.0 mm
Strap Width max. (G)	6.0 mm
Width (W)	12.0 mm

Specifications

ELV compliant (Article 4 - 2)	YES
Hazardous good	No
Operating Temperature - °C	-40 °C to +85 °C
Specifications	RoHS ✓