

# Product datasheet

Specifications



## Thorsman TET 7-10 - grommet - grey - diameter 7 to 10

Local distributor code: 2228136    IMT37303

EAN Code : 3606480398834

### Main

|                      |              |
|----------------------|--------------|
| Product range        | Thorsman TET |
| Product type         | Grommet      |
| Colour               | Grey         |
| Quantity per package | Set of 50    |

### Complementary

|                      |           |
|----------------------|-----------|
| Material             | EPDM      |
| Cable outer diameter | 7...10 mm |
| Drilling diameter    | 19 mm     |

### Environment

|          |      |
|----------|------|
| IP-Class | IP67 |
|----------|------|

### Packing Units

|                              |           |
|------------------------------|-----------|
| Unit Type of Package 1       | PCE       |
| Number of Units in Package 1 | 1         |
| Package 1 Weight             | 5.16 g    |
| Package 1 Height             | 2.0 cm    |
| Package 1 width              | 2.5 cm    |
| Package 1 Length             | 2.5 cm    |
| Unit Type of Package 2       | S03       |
| Number of Units in Package 2 | 2000      |
| Package 2 Weight             | 10.768 kg |
| Package 2 Height             | 30.0 cm   |
| Package 2 width              | 30.0 cm   |
| Package 2 Length             | 40.0 cm   |
| Unit Type of Package 3       | BB1       |
| Number of Units in Package 3 | 50        |
| Package 3 Weight             | 258.0 g   |
| Package 3 Height             | 6.0 cm    |

|                  |         |
|------------------|---------|
| Package 3 width  | 7.0 cm  |
| Package 3 Length | 14.0 cm |

### Offer Sustainability

|                            |                                                                                                             |
|----------------------------|-------------------------------------------------------------------------------------------------------------|
| Sustainable offer status   | Green Premium product                                                                                       |
| REACH Regulation           | <a href="#">REACH Declaration</a>                                                                           |
| REACH free of SVHC         | Yes                                                                                                         |
| EU RoHS Directive          | Pro-active compliance (Product out of EU RoHS legal scope)<br><a href="#">EU RoHS Declaration</a>           |
| Toxic heavy metal free     | Yes                                                                                                         |
| Mercury free               | Yes                                                                                                         |
| RoHS exemption information | <a href="#">Yes</a>                                                                                         |
| China RoHS Regulation      | <a href="#">China RoHS declaration</a><br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure   | <a href="#">Product Environmental Profile</a>                                                               |

### Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|