


Double End Speed Wrench

3736M

- 5° gear action (72 teeth)
- Chrome vanadium alloy steel
- Chrome plated




KT NO.	Size mm	D1 mm	D2 mm	H1 mm	H2 mm	L mm		
37360809M	8 x 9	16.8	20.2	6.5	6.9	128	42	10 / 320
37361011M	10 x 11	20.2	21.8	7.3	7.7	150	61	10 / 200
37361013M	10 x 13	20.2	24.8	7.3	8.6	150	75	10 / 200
37361213M	12 x 13	23.0	24.8	8.2	8.6	170	88	10 / 200
37361415M	14 x 15	26.5	29.5	9.0	9.4	190	126	10 / 160
37361618M	16 x 18	29.5	33.5	9.9	10.7	210	182	10 / 120
37361719M	17 x 19	31.5	33.5	10.3	11.2	230	206	10 / 120

Double End Speed Wrench & Set

3737M

- 5° gear action (72 teeth)
- Reversible
- Take-up :13°
- Chrome vanadium alloy steel
- Chrome plated



KT NO.	Size mm	D1 mm	D2 mm	H1 mm	H2 mm	L mm		
37370607M	6 x 7	14.2	17.2	6.3	6.5	115	32	10 / 320
37370809M	8 x 9	16.8	20.2	6.5	6.9	128	42	10 / 320
37371011M	10 x 11	20.2	21.8	7.3	7.7	150	59	10 / 200
37371213M	12 x 13	23.0	24.8	8.2	8.6	170	87	10 / 200
37371415M	14 x 15	26.5	29.5	9.0	9.4	190	127	10 / 160
37371618M	16 x 18	29.5	33.5	9.9	10.7	210	178	10 / 120
37371719M	17 x 19	31.5	33.5	10.3	11.2	230	197	10 / 120
37372123M	21 x 23	40.0	46.0	13	14.5	260	413	8 / 64
37372224M	22 x 24	40.0	46.0	13	14.5	260	385	8 / 64




► Color box

KT NO.	PC.	Contents	Package		
12706MR	6	8 x 9, 10 x 11, 12 x 13, 14 x 15, 16 x 18, 17 x 19	Color box	0.72	1 / 16

Stubby Speed Wrench & Set

3738M

- Open-ended and ratchet ring-wrench
- 5° gear action (72 teeth)
- Chrome vanadium alloy steel
- Chrome plated



KT NO.	Size mm	D1 mm	D2 mm	H1 mm	H2 mm	L mm		
373810M	10	22.0	21.5	4.6	7.6	95	47	15 / 360
373811M	11	23.8	23.0	5.1	8.0	103	55	15 / 360
373812M	12	26.0	24.8	5.3	8.5	106	65	15 / 360
373813M	13	27.5	26.1	5.6	8.7	108	75	15 / 360
373814M	14	30.5	27.6	6.0	9.3	115	88	15 / 360

KT NO.	Size mm	D1 mm	D2 mm	H1 mm	H2 mm	L mm		
373815M	15	31.8	29.2	6.3	9.9	119	104	15 / 360
373816M	16	34.0	30.9	6.5	10.0	123	111	10 / 200
373819M	19	40.2	35.5	8.0	11.7	139	183	10 / 120