

46-12 Socket

AS HPQ

- extra deep
- bi-hexagon, 12 mm
- 3/8" $\square$ -drive
- use on glow plugs of diesel engines



Code	Type	Δ g	
02020012	BMW: 324d; 524d	57	10

Testing tools for car electrics

12905 Car circuit tester

- for car electrics 6-12 volt and 24 volt
- with pointed probe
- cover cap
- connecting lead with alligator clip



Code	L mm	Δ g	
77380001	120	73	10

7756 Automotive voltage tester (complete set)

- testing unit for electric and electronic car components
- 3-48 volt
- 2 LEDs to indicate voltage and plus or minus pole
- complete in Pc-bag



Content:
1 basic unit with 1.5 m cable, testing tip, integrated mechanical sliding needle
1 crocodile terminal
1 jaw clamp

Code	Δ g	
77560002	100	1

Special tools for brakes and wheels

ES 721/15/3/2

- 530 x 350 x 40 mm
- 6 pieces



Code	Δ g
96838172	5060

No	Content
2309K	1/2" $\square$ 17; 19; 21 mm
721/15 Quick 35c Pkw	30-150 N·m 17; 19; 22 mm; $\blacksquare$ 1/2"
10599/2	245 mm

34c/35c Wheel braces

- DIN 3119/ISO 6788
- forged centre section, pressed-in extension arms with extra deep forged socket heads
- Chrome Alloy Steel, chrome plated



Code	No	$\square$ mm/"	L mm	Δ g	
43030005	34c Lkw	24; 27; 32; $\blacksquare$ 3/4"	400	2058	1
43030006	35c Pkw	17; 19; 22; $\blacksquare$ 1/2"	400	5020	1

39 Tyre levers

- handy, sturdy construction, purposefully shaped
- Chrome Alloy Steel



Code	No	L mm	Δ g	
74010401	39 Pkw	400	358	5
74010601	39/1 Lkw	600	897	5
74010602	39/1 Lkw	600	1180	5
74010603	39/1 Lkw	600	900	5