

735/40 Ratchet insert tool

- reversible
- 3/4" ■-drive
- for use with Service-MANOSKOP® torque wrench No 730/40 Quick



Code	Typ	mm	g	
58 25 00 40	VW/Audi	14x18	515	1

1421 Bit screwdriver socket

- for inside TORX® screws
- outside ● 1/4" C 6.3 size T45
- length 26 mm
- for use on door hinges
- drive tools: f.e. ratchet reversible No 725/4B and ratchet tap holder No 1820 or ratchet reversible No 725/4B and torque wrench



Code	Type	g	
08 13 00 45	VW: Golf III	8	10

1068 Air filter claw


- for loosening of filter cartridges on air brakes (trucks)



Code	Clamp. width "	total height mm	length of claws mm	g	
74 62 00 11	1/2	100-145	85	60	925 1

2509 IMPACT sockets

- 3/4" ○-drive
- for power drivers
- extra deep
- with reduced diameter
- Chrome Alloy Steel, gunmetal finish




Code	mm	d ₁ mm	d ₂ mm	L mm	t mm	g	
25 09 00 27	27	40.5	44	100	72.5	672	2
25 09 00 30	30	44.3	44	100	72.5	728	2
25 09 00 32	32	46.8	44	100	72	778	2
25 09 00 33	33	48	44	100	72	803	2

for Trilux wheels

2609 IMPACT sockets

- 1" ○-drive
- for power drivers
- extra deep
- with reduced outside diameter
- Chrome Alloy Steel, gunmetal finish



Code	mm	d ₁ mm	d ₂ mm	L mm	t mm	g	
26 09 00 27	27	42.3	54	110	80	1001	2
26 09 00 30	30	46	54	110	79.5	1047	2
26 09 00 32	32	48.5	54	110	79	1015	2
26 09 00 33	33	49.8	54	110	78.5	1102	2

for wheel nuts

Special tools for HGVs

34c Lkw Wheel brace

- DIN 3119/ISO 6788
- forged centre section, pressed-in extension arms with extra deep forged socket heads
- Chrome Alloy Steel, chrome plated



Code	mm/"	L mm	g	
43 03 00 05	24; 27; 32; ■ 3/4"	400	2058	1

39 Tyre levers

- handy, sturdy construction, purposefully shaped
- Chrome Alloy Steel



Code	No	L mm	g	
74 01 06 01	39/1 Lkw	600	897	5
74 01 06 02	39/1 Lkw	600	1180	5
74 01 06 03	39/1 Lkw	600	900	5