

Tube tools, other tools

12900/3 Tyre-tread Vernier gauge

- sturdy brass construction
- smooth ground surface



Code	measuring range mm	△ g	g	g
77371004	30	41	1	

12900/4 Electronic tyre-tread Vernier gauge

- large LCD display with clear read-offs, figures 9.5 mm high
- display accuracy 0.01 mm/ 0.0005"
- ON/OFF push button
- unit of measure switchable mm/inch
- zeroing possible in any position
- incl. 1 x 3 V battery (type CR2032) packaged in accordance with UN 3091, Class 9



Code	measuring range mm/"	△ g	g	g
77371005	25/1	60	1	

12935 Tape measure

- with tape lock
- metric-inch scales



Code	size	L m	△ g	g	g
77040010	3	3	92	10	
77040011	5	5	164	10	

13110 Steel rule

- metric-inch scales
- length 300 mm



Code	Divisions Top Edge "	Divisions Lower Edge mm	△ g	g	g
77460001	1/16, 1/32, 1/64	0.5; 1	26	5	

12915 Ratchet tap holders

- with ratchet
- steel
- chrome plated



Code	size	Capacity mm	DIN ¹⁾	ISO ²⁾	L mm	△ g	g	g
77390001	1	2.0-5.0	M3-8	M1-6	85	180	1	
77390002	2	4.6-8	M5-12	M6-12	110	305	1	

¹⁾ for taps DIN

²⁾ for taps ISO

12932 Padlock



Code	△ g	g	g
77210002	85	1	

12250 Force feed oil can

- metal container
- brass pump
- Content: 500 ccm



Code	△ g	g	g
77010001	275	1	

12251 Plastic oil can

- made of plastic
- Content: 250 ccm



Code	△ g	g	g
77110002	60	5	

12320 Electricians cable knife

- with stainless blade



Code	Blade mm	△ g	g	g
77020000	90	78	10	

12321 Scribing iron

- with knurled centre-section
- 1 straight and 1 offset blade
- blades gunmetal finished



Code	L mm	△ g	g	g
77100000	250	31	10	