

1202

Bit box

NEW

- storage box with screwdriver bits
 - 20 bits stored in a robust, space-saving box
 - box with internal hex drive for rapid application
- Content:
- 1 bit holder with quick-action chuck and magnet
 - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
 - ⊕ 3 bits, PZ1; PZ2; PZ3 for POZIDRIV/SUPADRIV® screws
 - ⊖ 4 bits, sizes 0.6 x 3.5; 0.8 x 4.0; 1.0 x 5.5; 1.2 x 6.5 mm for slotted screws
 - 4 bits, sizes T15; T20; T25; T30 for inside TORX® screws
 - 3 bits, sizes T20; T25; T30 for inside TORX® screws (TORX® TAMPER RESISTANT)
 - 3 bits, sizes 4; 5; 6 mm for inside hexagon screws



Code

g

96080110

222 1

1203

Bit box

NEW

- storage box with screwdriver bits
 - compact: plenty of tools - less space needed
 - incl. convenient stand-up action
- Content:
- 1 bit holder with quick-action chuck and magnet
 - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
 - ⊕ 3 bits, PZ1; PZ2; PZ3 for POZIDRIV/SUPADRIV® screws
 - 4 bits, sizes 3; 4; 5; 6 mm for inside hexagon screws



Code

g

96080115

110 10

1204/21-1

Bit box

- storage box with screwdriver bits
- Content:
- 1 magnetic bit-holder
 - ⊕ 4 bits, PH1; PH2 (2x); PH3 for Phillips screws
 - ⊕ 4 bits, PZ1; PZ2 (2x); PZ3 for POZIDRIV/SUPADRIV® screws
 - 9 bits, sizes T10; T15; T20 (2x); T25 (2x); T27; T30; T40; for inside TORX® screws
 - 3 bits, sizes 4; 5; 6 mm; for inside hexagon screws



Code

g

96080121

186 1

1204/21-2

Bit box

- storage box with screwdriver bits
- Content:
- 1 magnetic bit-holder
 - ⊕ 3 bits, PH1; PH2; PH3 for Phillips screws
 - ⊖ 4 bits, sizes 0.5 x 4.0; 0.6 x 4.5; 0.8 x 5.5; 1.2 x 6.5 mm; for slotted screws
 - 6 bits, sizes T10; T15; T20; T25; T30; T40; for inside TORX® screws
 - 3 bits, sizes 4; 5; 6 mm; for inside hexagon screws
 - ⊕ 4 bits, sizes 4; 6; 8; 10 mm; for TORQ-SET® screws



Code

g


96080122

181 1

4000

Spinner handles

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- handle of impact proof plastic
- internal hex drive with a collar-thrust spring
- bits are easy to insert, lock securely in position and can be removed just as easily; even hex bits with a wide groove (Type E, DIN 3126/ISO 1173)



Code

mm " d mm L₁ mm L₂ mm g

18073026

D 6.3 1/4 11 75 190 119 5

inside ○ DIN 3126/ISO 1173

4006/1

Spinner with magazine holder

- for 6 bit screwdriver bits (25 mm) with 1/4" outer hexagon
- DIN 3126/ISO 1173 C 6.3
- transparent plastic handle for storing bits with rotating selection cap
- internal hexagon and powerful permanent magnet



Code

mm " d mm L₁ mm L₂ mm g

18080017

D 6.3 1/4 10 120 230 124 1

inside ○ DIN 3126/ISO 1173

12504

Bit holder

- for bit screwdriver bits with outside hexagon 1/4"
- DIN 3126/ISO 1173 C 6.3
- flexible shaft



Code

mm " L₁ mm L₂ mm g

18103016

D 6.3 1/4 175 290 168 10

inside ○ DIN 3126/ISO 1173