

Product data sheet

700 020 3

Cable shear D20



- For cutting single-strand, multi-strand and fine-wire aluminum and copper cables
- Not for steel wire, wire cable or hard-drawn copper cable
- Easy, clean cut with one-hand operation
- No crushing or deformation of cables
- Initial and final cut (1st and 2nd blades) allow cable diameter up to 20 mm respectively AWG 2/0 to be cut
- Various handle options

General

Item number	700 020 3
EAN	4049002006630
Weight	300 g
Dimension	200 mm
Dimension packaging	20 x 50 x 220 mm

Specifications

Finish	black-oxide finish
Max cable dia.	20 mm
Single conductor cable, solid (Cu)	Cu 16 mm ²
Single conductor cable, solid (AL)	Al 50 mm ²
Multi-conductor cable (Cu)	Cu 70 mm ²
Multi-conductor cable (AL)	Al 70 mm ²
Fine-stranded cable (Cu)	Cu 95 mm ²
Grips	Plastic-coated grips

Classification

eCl@ss 10.1	ADS511008
ETIM 7.0	EC000142
proficl@ss 7.0	EAD256c001

With reservations regarding technical modifications and errors. Illustration may vary.