

# Universal Socket & Set

KT No. & D1



## 3750M


- Chrome vanadium alloy steel
- DIN 3120

| KT NO.  | mm | D1 mm | D2 mm | ℓ mm | L mm |    |          |
|---------|----|-------|-------|------|------|----|----------|
| 375010M | 10 | 14.5  | 19    | 9    | 49.5 | 56 | 15 / 240 |
| 375011M | 11 | 15.8  | 19    | 10   | 50.5 | 57 | 15 / 240 |
| 375012M | 12 | 17.0  | 19    | 10   | 51.0 | 57 | 15 / 240 |
| 375013M | 13 | 18.3  | 19    | 11   | 52.0 | 56 | 15 / 240 |
| 375014M | 14 | 20.0  | 19    | 11   | 52.0 | 60 | 12 / 192 |
| 375015M | 15 | 22.0  | 19    | 13   | 54.5 | 66 | 10 / 160 |
| 375016M | 16 | 22.0  | 19    | 13   | 54.5 | 63 | 10 / 160 |
| 375017M | 17 | 24.0  | 19    | 14   | 55.5 | 71 | 8 / 128  |
| 375018M | 18 | 26.0  | 19    | 14   | 55.5 | 75 | 6 / 96   |
| 375019M | 19 | 26.0  | 19    | 16   | 57.5 | 72 | 6 / 96   |

## 3750S

3/8"

- Chrome vanadium alloy steel



| KT NO.  | inch  | D1 mm | D2 mm | ℓ mm | L mm |    |          |
|---------|-------|-------|-------|------|------|----|----------|
| 375012S | 3/8   | 14.0  | 19    | 9    | 49.0 | 56 | 15 / 240 |
| 375014S | 7/16  | 15.8  | 19    | 10   | 50.5 | 58 | 15 / 240 |
| 375016S | 1/2   | 18.3  | 19    | 11   | 52.0 | 59 | 15 / 240 |
| 375018S | 9/16  | 20.0  | 19    | 11   | 52.0 | 60 | 12 / 192 |
| 375020S | 5/8   | 22.0  | 19    | 13   | 54.5 | 65 | 10 / 160 |
| 375022S | 11/16 | 24.0  | 19    | 14   | 55.5 | 65 | 8 / 128  |
| 375024S | 3/4   | 26.0  | 19    | 16   | 57.5 | 74 | 6 / 96   |

## 3709MR10

3/8"

- Socket rail 240mmL



9 PC.

Contents

0.6 14

3750M 10, 11, 12, 13, 14, 16, 17, 18, 19

8730909

## 3707SR10

3/8"

- Socket rail 240mmL



7 PC.

Contents

0.48 14

3750S 3/8, 7/16, 1/2, 9/16, 5/8, 11/16, 3/4

8730907

