

BU-4061-N-XX-@ (UL® Listed Test Probe PCV Wire)



- 4mm, Straight, Shrouded, Banana Plug
- Uses 18 AWG (65/36) UL 1855, with a flexible PVC jacket.
- Length is designated in inches by the “XX” in the part number.
Standard lengths are: 12”, 18”, 24”, 39”, 48”, 60” and 72”
- Material: Probe – Stainless Steel, #8-32 threads for attachments
Banana Plug – Nickel plated Beryllium Copper and Brass
Cover -- Polypropylene
- Ratings:
 - o Operating Voltage: 1,000V CAT III
 - o Current: 20 Amps
 - o Operating Temperature: -40°C to 80°C
- Color: The “@” in the model number represents color. Available colors:
-0 Black, -2 Red, -4 Yellow, -5 Green, -6 Blue, -8 Gray, -9 White
- RoHS 3 Compliant, CE Certified