





## NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4  
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA @12VDC
- ▲ 5. CONTACT MATERIAL: SILVER
6. TRAVEL: 0.30±0.15mm
7. OPERATING FORCE: 160±50gf
8. CONTACT RESISTANCE: 100mΩ MAX.
- ▲ 9. ELECTRICAL LIFE: 100,000 CYCLES MIN
10. ▲ DENOTES CRITICAL DIMENSION



|     |        |             |         |     |
|-----|--------|-------------|---------|-----|
| B   | 21512  | REDRAW      | 7/15/14 | EBP |
| REV | PCR NO | DESCRIPTION | DATE    | BY  |

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY  
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE TL1100CF160Q.08BLK

|       |                |        |             |       |
|-------|----------------|--------|-------------|-------|
| SCALE | DATE 7/15/2014 | DR EBP | DWG XP0038A | REV B |
|-------|----------------|--------|-------------|-------|