





NOTES:

1. ALL DIMENSIONS IN MM [INCH].
2. GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
3. TERM. NOS. FOR REFERENCE ONLY.
4. RATING: 50mA @ 50VDC
- ▲ 5. OPERATING FORCE: 160 ± 50 gf
6. TRAVEL: 0.25 +0.20/-0.10 mm
7. CONTACT RESISTANCE: 100 MILLI-OHMS MAX. (INITIAL)
8. MECHANICAL/ELECTRICAL LIFE: 100,000 CYCLES MIN.
- ▲ 9. CONTACT MATERIAL: SILVER
10. ▲ DENOTES CRITICAL PARAMETER.
11. OPERATING TEMP: -40°C to 85°C



TITLE TL1105JAF160Q1RBLK

SCALE
4:1DATE
9/20/2006DR
MWDWG
XP0189PREV
D

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

D	24728	update print and correct Oper. Force	2/10/21	MW
C	20600	ADDED TERMINAL NUMBERS, 3D MODELED	05/10/12	drg
REV	PCR NO	DESCRIPTION	DATE	BY