


RoHS compliant



PCB Layout
tolerances +/-0.1

MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 125V
- Current rating: 7.5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >5GΩ
- Temperature range: -55° to +125°C

General tolerances (Delttron standard)				
size in mm	> 0.5 up to 3	> 3 up to 6	> 6 up to 30	> 30 up to 120
	tolerances	tolerances	tolerances	tolerances
	±0.1	±0.2	±0.2	±0.3

modification	Rev. a) ?? nf	Rev.	Rev.	DE002564		
	Rev.	Rev.	Rev.	part no.		
DTS25SYC/2M66UN			1.5:1	drawn	06.10.2009	nf
			scale	checked		
				approved		
DELTRON SWISS CONNECT 2 CUSTOMIZE			Industrie Neuohof 8c CH-3422 Kirchberg www.d-sub.swiss			
			K053006 a drawing no.			