






RoHS compliant



MATERIALS

- Insulator: Thermoplastic UL 94-V-0 white
- Contact: Machined / Copper alloy
- Contact finish: Quality class 2
- Shell: steel tin plated

CHARAKTERISTICS

- Working voltage: 60V
- Current rating: 5A
- Contact resistance: max. 10mΩ - DIN41652
- Insulation resistance: >5GΩ
- Temperature range: -55° to +125°C

General tolerances (Delftron standard)			
size in mm		tolerances	
> 0.5	> 3	> 6	> 30
up to 3	up to 6	up to 30	up to 120
±0.1	±0.2	±0.2	±0.3

	All dimensions in mm	Rev.	Rev.	Rev.	DE013198		
		Rev.	Rev.	Rev.	part no.		
HD-D78SY/2M86UN				1.2:1	drawn	09.01.2019	mw
				scale	checked		
					approved		
				K063339			
Industrie Neuhof 8c CH-3422 Kirchberg www.d-sub.swiss				drawing no.			