

RUBBER BACKING PAD

338.00	Ø 125 mm - gambo Ø 6 mm	10	338002
338.05	Ø 180 mm - bore Ø 16 mm	10	338057
338.08	Ø 180 mm - bore Ø 16 mm	10	338088

NYLON BACKING PAD

338.10	Ø 100 mm - bore Ø 10 mm	10	338101
338.20	Ø 115 mm - bore Ø 14 mm	10	338200
338.22	Ø 178 mm - bore Ø 14 mm	10	338224
338.25	Ø 100 mm - bore Ø 10 mm	10	338255
338.30	Ø 115 mm - bore Ø 10 mm	10	338309
338.35	Ø 115 mm - bore Ø 14 mm	10	338354
338.40	Ø 115 mm - bore Ø 16 mm	10	338408
338.45	Ø 125 mm - bore Ø 14 mm	10	338453
338.50	Ø 125 mm - bore Ø 16 mm	10	338507
338.55	Ø 150 mm - bore Ø 14 mm	10	338552
338.60	Ø 150 mm - bore Ø 16 mm	10	338606
338.65	Ø 178 mm - bore Ø 14 mm	10	338651
338.70	Ø 178 mm - bore Ø 16 mm	10	338705

VELCRO BACKING PAD

shank Ø 10 mm - bore M14

338.80	Ø 115 mm	5	338804
338.82	Ø 125 mm	5	338828
338.85	Ø 150 mm	5	338859