

VELCRO ABRASIVE SHEETS with dust extraction holes - **93** mm

348.30	5 sheets grain 40	☒	348308
348.31	25 sheets grain 40	☐	348315
348.35	5 sheets grain 60	☒	348353
348.36	25 sheets grain 60	☐	348360
348.40	5 sheets grain 80	☒	348407
348.41	25 sheets grain 80	☐	348414
348.45	5 sheets grain 120	☒	348452
348.46	25 sheets grain 120	☐	348469
348.50	5 sheets grain 240	☒	348506
348.51	25 sheets grain 240	☐	348513
348.56	25 sheets assorted grades	☐	348568

VELCRO ABRASIVE DISCS - **ø 115** mm

349.00	10 sheets grain 40	☒	349008
349.01	25 sheets grain 40	☐	349015
349.10	10 sheets grain 120	☒	349107
349.11	25 sheets grain 120	☐	349114
349.20	10 sheets grain 240	☒	349206
349.21	25 sheets grain 240	☐	349213
349.30	10 sheets assorted grades	☒	349305
349.31	25 sheets assorted grades	☐	349312

VELCRO ABRASIVE DISCS - **ø 125** mm

349.55	10 sheets grain 40	☒	349558
349.56	25 sheets grain 40	☐	349565
349.60	10 sheets grain 120	☒	349602
349.61	25 sheets grain 120	☐	349619
349.65	10 sheets grain 240	☒	349657
349.66	25 sheets grain 240	☐	349664
349.70	10 sheets assorted grades	☒	349701
349.71	25 sheets assorted grades	☐	349718