

VELCRO ABRASIVE DISCS with dust extraction holes - ø **115** mm

349.33	10 discs grain 40	10	349336
349.34	25 discs grain 40	1	349343
349.35	10 discs grain 80	10	349350
349.36	25 discs grain 80	1	349367
349.40	10 discs grain 120	10	349404
349.41	25 discs grain 120	1	349411
349.45	10 discs grain 240	10	349459
349.46	25 discs grain 240	1	349466
349.50	10 sheets assorted grades	10	349503
349.51	25 sheets assorted grades	1	349510

**VELCRO ABRASIVE DISCS** with dust extraction holes - ø **125** mm

349.73	10 discs grain 40	10	349732
349.74	25 discs grain 40	1	349749
349.75	10 discs grain 80	10	349756
349.76	25 discs grain 80	1	349763
349.80	10 discs grain 120	10	349800
349.81	25 discs grain 120	1	349817
349.85	10 discs grain 240	10	349855
349.86	25 discs grain 240	1	349862
349.90	10 sheets assorted grades	10	349909
349.91	25 sheets assorted grades	1	349916

**VELCRO ABRASIVE DISCS** with dust extraction holes - ø **150** mm

349.95	10 discs grain 40	10	349954
349.96	10 discs grain 80	10	349961
349.97	10 discs grain 120	10	349978
349.98	10 discs grain 240	10	349985
349.99	10 sheets assorted grades	10	349992

