

ref.

description

pack
q.tyEAN13
8011017**SANDING****DRUM SANDER**

357.96	ø 45 x 30 mm - shank ø 6 mm	10	357966
357.98	3 sanding belts assorted grades for art. 357.96	10	357980

ROTARY FLAP SANDER shank ø 6 mm - grain 80

358.40	ø 40 x 20 mm	10	358406
358.50	ø 50 x 20 mm	10	358505
358.60	ø 60 x 40 mm	10	358604
358.80	ø 80 x 30 mm	10	358802
358.90	40 assorted rotary flap sanders in display box 15 ø 40 x 20 mm 15 ø 50 x 20 mm 10 ø 60 x 30 mm	1	358901

**ROTARY FLAP SANDER**

ø x thickness x shank	RPM	grain 60		grain 80		grain 120	
		ref.	EAN13 8011017	ref.	EAN13 8011017	ref.	EAN13 8011017
30 x 10 x 6*	22900	RG.002	085241	RG.037	085418	RG.072	085586
30 x 15 x 6*	22900	RG.004	085258	RG.039	085425	RG.074	085593
30 x 20 x 6*	22900	RG.006	085265	RG.041	085432	RG.076	085609
40 x 10 x 6	17100	RG.011	085272	RG.046	085449	RG.081	085616
40 x 15 x 6	17100	RG.012	085289	RG.047	085456	RG.082	085623
40 x 20 x 6	17100	RG.013	085296	RG.048	085463	RG.083	085630
40 x 30 x 6	17100	RG.015	085302	RG.050	085470	RG.085	085647
50 x 20 x 6	13700	RG.019	085319	RG.054	085487	RG.089	085654
50 x 30 x 6	13700	RG.021	085326	RG.056	085494	RG.091	085661
60 x 20 x 6	11400	RG.024	085333	RG.059	085500	RG.094	085678
60 x 30 x 6	11400	RG.026	085340	RG.061	085517	RG.096	085685
60 x 40 x 6	11400	RG.027	085357	RG.062	085524	RG.097	085692
60 x 50 x 6	11400	RG.028	085364	RG.063	085531	RG.098	085708
80 x 15 x 6	8500	RG.029	085371	RG.064	085548	RG.099	085715
80 x 30 x 6	8500	RG.032	085388	RG.067	085555	RG.102	085722
80 x 40 x 6	8500	RG.033	085395	RG.068	085562	RG.103	085739
80 x 50 x 6	8500	RG.034	085401	RG.069	085579	RG.104	085746

* On demand available with shank ø 3 mm - Packing: 10 pcs.

☒ PG pack☐ neutral pack