

Ø x
thickness
x hole

ref.

EAN13
8011017

Ø x
thickness
x hole

ref.

EAN13
8011017

Ø x
thickness
x hole

ref.

EAN13
8011017

**CUTTING AND
GRINDING**

MOUNTED GRINDING POINT - PINK CORUNDUM CONICAL SHAPE F

8 x 12 x 3	MF.001	084671	20 x 25 x 6	MF.004	084701	30 x 40 x 6	MF.007	084732
10 x 15 x 3	MF.002	084688	25 x 30 x 6	MF.005	084718			
10 x 15 x 6	MF.003	084695	30 x 30 x 6	MF.006	084725			



ROUNDED SHAPE G

20 x 10 x 6	MG.001	084756	40 x 10 x 6	MG.003	084770			
30 x 10 x 6	MG.002	084763	40 x 20 x 6	MG.004	084787			



DOUBLE CHAMFER SHAPE H

20 x 6 x 6	MH.001	084794	40 x 10 x 6	MH.003	084817			
30 x 10 x 6	MH.002	084800	50 x 10 x 6	MH.004	084824			




ROUND HEAD SHAPE I

10 x 10 x 3	MI.001	084831	15 x 15 x 6	MI.004	084862	30 x 30 x 6	MI.007	084893
10 x 20 x 6	MI.002	084848	20 x 20 x 6	MI.005	084879			
12 x 12 x 6	MI.003	084855	25 x 25 x 6	MI.006	084886			




POINTED ARCH SHAPE L

6 x 10 x 3	ML.001	084916	10 x 15 x 6	ML.004	084947	18 x 32 x 6	ML.007	084978
8 x 10 x 3	ML.002	084923	12 x 20 x 6	ML.005	084954	20 x 40 x 6	ML.008	084985
8 x 10 x 6	ML.003	084930	15 x 20 x 6	ML.006	084961			



CUP SHAPE M

10 x 20 x 3	MM.001	084992	20 x 20 x 6	MM.004	085029	30 x 30 x 6	MM.007	085050
12 x 20 x 6	MM.002	085005	20 x 30 x 6	MM.005	085036	40 x 20 x 6	MM.008	085067
15 x 20 x 6	MM.003	085012	30 x 20 x 6	MM.006	085043	40 x 30 x 6	MM.009	085074



TRUNCATED-CONE SHAPE N

8 x 10 x 3	MN.001	085081	12 x 20 x 6	MN.004	085111	25 x 40 x 6	MN.007	085142
8 x 15 x 3	MN.002	085098	15 x 25 x 6	MN.005	085128			
10 x 15 x 6	MN.003	085104	20 x 30 x 6	MN.006	085135			



Packing: 10 pcs

☐ PG pack

☐ neutral pack