

GRINDING WHEEL - GREY CORUNDUM

400.00	ø 75 x 10 mm - hole ø 10 mm	10	400006
402.00	ø 75 x 10 mm - hole ø 13 mm	10	402000
403.00	ø 75 x 10 mm - hole ø 13 mm - SILICON CARBIDE	10	403007
404.00	ø 100 x 12 mm - hole ø 13 mm	10	404004
404.50	ø 125 x 15 mm - hole ø 16 mm	10	404509
405.00	ø 150 x 20 mm - hole ø 16 mm	10	405001

WET GRINDING WHEEL - WHITE CORUNDUM

880.00	ø 100 x 20 x 16 mm for drills with ø 43 mm collar - CE	1	880006
882.00	replacement grinding wheel ø 100 x 20 x 16 mm for art. 880.00	1	882000

WHEEL DRESSERS C48 20T - SILICON CARBIDE

dimensions	ref.	
150 x 20	C48.01	
200 x 20	C48.02	
200 x 25	C48.03	

Packing: 1 pcs.

DOUBLE GRAIN WET STONES

dimensions	C49 green silicon carbide grain 120/400		A99 ruby corundum grain 150/320	
leng. x width x thick.	ref.		ref.	
125 x 50 x 20	DG.01		DG.03	
150 x 50 x 25	DG.02		DG.04	

Packing: 1 pcs.

ABRASIVE FILES - PINK CORUNDUM

SHAPE	dimensions	grain 80		grain 120		grain 220	
		ref.		ref.		ref.	
triangular	100 x 13	LTR.001		LTR.004		LTR.007	
	150 x 16	LTR.002		LTR.005		LTR.008	
	200 x 20	LTR.003		LTR.006		LTR.009	
half-round	100 x 13	LTO.001		LTO.004		LTO.007	
	150 x 16	LTO.002		LTO.005		LTO.008	
	200 x 20	LTO.003		LTO.006		LTO.009	
square	100 x 13	LQU.001		LQU.004		LQU.007	
	150 x 16	LQU.002		LQU.005		LQU.008	
	200 x 20	LQU.003		LQU.006		LQU.009	

Packing: 10 pcs.

☐ PG pack☐ neutral pack