

**FORSTNER BIT - DIN 7483**
**90 mm lenght - shank ø 8 mm**

|               |                                       |   |        |
|---------------|---------------------------------------|---|--------|
| <b>12.010</b> | ø <b>10</b> mm                        | 1 | 120102 |
| <b>12.012</b> | ø <b>12</b> mm                        | 1 | 120126 |
| <b>12.014</b> | ø <b>14</b> mm                        | 1 | 120140 |
| <b>12.015</b> | ø <b>15</b> mm                        | 1 | 120157 |
| <b>12.016</b> | ø <b>16</b> mm                        | 1 | 120164 |
| <b>12.018</b> | ø <b>18</b> mm                        | 1 | 120188 |
| <b>12.020</b> | ø <b>20</b> mm                        | 1 | 120201 |
| <b>12.022</b> | ø <b>22</b> mm                        | 1 | 120225 |
| <b>12.024</b> | ø <b>24</b> mm                        | 1 | 120249 |
| <b>12.025</b> | ø <b>25</b> mm                        | 1 | 120256 |
| <b>12.026</b> | ø <b>26</b> mm                        | 1 | 120263 |
| <b>12.028</b> | ø <b>28</b> mm                        | 1 | 120287 |
| <b>12.030</b> | ø <b>30</b> mm                        | 1 | 120300 |
| <b>12.032</b> | ø <b>32</b> mm - shank ø <b>10</b> mm | 1 | 120324 |
| <b>12.034</b> | ø <b>34</b> mm - shank ø <b>10</b> mm | 1 | 120348 |
| <b>12.035</b> | ø <b>35</b> mm - shank ø <b>10</b> mm | 1 | 120355 |
| <b>12.036</b> | ø <b>36</b> mm - shank ø <b>10</b> mm | 1 | 120362 |
| <b>12.040</b> | ø <b>40</b> mm - shank ø <b>10</b> mm | 1 | 120409 |
| <b>12.045</b> | ø <b>45</b> mm - shank ø <b>10</b> mm | 1 | 120454 |
| <b>12.050</b> | ø <b>50</b> mm - shank ø <b>10</b> mm | 1 | 120508 |

