

POZIDRIV BITS - 25 mm length

459.90	2 bits n. 0	10	459905
460.00	2 bits n. 1	10	460000
460.10	2 bits n. 2	10	460109
460.20	2 bits n. 3	10	460208
460.30	1 bits n. 4	10	460307

TITANIUM POZIDRIV BITS - 25 mm length

460.50	2 bits n. 0	5	460505
460.52	2 bits n. 1	5	460529
460.54	2 bits n. 2	5	460543
460.56	2 bits n. 3	5	460567

DOUBLE FUNCTION BIT - 60 mm length

461.00	slot 0,8 x 4 mm + Phillips n. 1	10	461007
462.00	slot 0,8 x 5 mm + Phillips n. 2	10	462004
462.50	slot 1,2 x 7,2 mm + Phillips n. 3	10	462509

BITS ASSORTMENT

463.00	7 pcs: magnetic bit holder + Phillips 1 - 2 + Pozidriv 1 - 2 + slot 4 - 5 mm	5	463001
464.00	10 pcs: magnetic bit holder + Phillips 1 - 2 - 3 + Pozidriv 1 - 2 - 3 + slot 4 - 5 - 6 mm	5	464008
PG32A	32 pcs: quick magnetic bit holder + Phillips 1 - 2 - 3 - 4 + Pozidriv 1 - 2 - 3 - 4 + slot 3 - 4 - 5 - 6 mm + hexagonal 3 - 4 - 5 - 6 mm + T10 - T15 - T20 - T25 - T27 - T30 - T40 + Torx holed T10 - T15 - T20 - T25 - T27 - T30 - T40 + square adapter 1/4" to 1/4" hexagonal	1	071046