

JIGSAW BLADES - BLACK & DECKER - SKIL FITTING

HSS - for metal

684.00	3 blades - coarse cutting	10	684000
685.00	3 blades - medium cutting	10	685007
686.00	3 blades - fine cutting	10	686004
686.50	3 blades - medium cutting - 80 mm length	10	686509

HSS HIGH SPEED STEEL

CV - for wood

687.00	3 blades - coarse cutting	10	687001
688.00	3 blades - medium cutting	10	688008
689.00	3 blades - fine cutting	10	689005
689.10	3 blades - coarse cutting - grounded blade	10	689104
689.20	3 blades - medium cutting - grounded blade	10	689203
689.50	3 blades - medium cutting - 100 mm length	10	689500
720.00	3 blades - medium cutting - for cutting curves	10	720005

CV CHROME VANADIUM

CV CHROME VANADIUM

CV CHROME VANADIUM

HARD METAL - for glass, tiles, bricks and plastic laminates

724.00	1 blade	5	724003
--------	---------	---	--------

HM HARD METAL

KIT 10 JIGSAW BLADES - BLACK & DECKER - SKIL FITTING

720.90	3 CV blades coarse cutting for wood + 3 CV blades medium cutting for wood + 2 CV blades cutting curves for wood + 2 HSS blades fine cutting for metal	3	720906
--------	---	---	--------



PG pack

neutral pack