

CARPENTER CLAMP

948.00	max opening 150 mm	6	948003
948.10	max opening 200 mm	6	948102
948.20	max opening 250 mm	6	948201
948.30	max opening 300 mm	6	948300
948.40	max opening 400 mm	4	948409
948.50	max opening 500 mm	4	948508
948.60	max opening 600 mm	4	948607
948.65	max opening 700 mm	2	948652
948.70	max opening 800 mm	2	948706
948.80	max opening 1000 mm	2	948805
948.82	max opening 1200 mm	2	948829
948.84	max opening 1500 mm	2	948843



ONE HAND CLAMP

948.93	max opening 150 mm	4	948935
948.95	max opening 300 mm	4	948959
948.97	max opening 450 mm	4	948973



ALUMINIUM "C" CLAMP

With quick adjustment and steel spindle

949.00	80 x 65 mm	1	949000
949.10	105 x 75 mm	1	949109
949.20	160 x 75 mm	1	949208



PG pack



neutral pack