



CV CIRCULAR SAW BLADE

ø mm		n. teeth	RPM	ref.	q.ty	EAN13 8011017
est.	bore					
125	20	24	7000	740.00	5	740003
125	20	80	7000	745.00	5	745008
150	20	24	7000	750.00	5	750002
150	20	80	7000	755.00	5	755007

With **2** bushes for adapting the bore: **20/13** mm and **20/16** mm

CARBIDE TIPPED CIRCULAR SAW BLADE
ALTERNATE TEETH

ø mm		n. teeth	suitable with:	RPM	ref.	q.ty	EAN13 8011017
est.	bore						
125	20	18	Bosch - Festo - Haffner - Hitachi - Mafell - Metabo - Ulmia	13000	756.02	1	756028
150	20	20	AEG - B&D - Bosch - Elu - Fein - Hitachi - Kress - Mafell - Metabo - Peugeot - Scheer - Skil - Wegoma	13000	756.10	1	756103
150	30	36		13000	756.12	1	756127
160	20	24	AEG - B&D - Bosch - Einhell - Fein - Festo - Haffner - Hitachi - Holz Her - Kress - Mafell - Makita - Narex - Peugeot - Protool - Rockwell - Ryobi - Scheer - Skil - Ulmia	9500	756.14	1	756141
160	20	36		9500	756.16	1	756165
170	30	18	Bosch - Elu - Festo - Haffner - Hitachi - Holz Her - Mafell - Makita - Metabo - Skil	9500	756.18	1	756189
170	30	36		9500	756.20	1	756202
180	30	36	B&D - Bosch - Elu - Festo - Haffner - Hitachi - Holz Her - Mafell - Makita - Metabo - Peugeot - Ryobi - Skil	9500	756.24	1	756240
180	30	52		9500	756.26	1	756264
190	30	42	AEG - B&D - Bosch - DeWalt - Elu - Festo - Hitachi - Holz Her - Kress - Mafell - Makita - Metabo - Protool - Scheer - Skil - Stayer	9500	756.30	1	756301
200	30	42	AEG - B&D - Bosch - Festo - Haffner - Hanning - Holz Her - Kity - Mafell - Makita - Ryobi - Scheer - Ulmia	9500	756.32	1	756325
210	30	30	AEG - B&D - Bosch - Elektra Beckum - Elu - Fein - Haffner - Hitachi - Holz Her - Mafell - Makita - Metabo - Skil - Stayer	9500	756.38	1	756387
210	30	42		9500	756.40	1	756400
230	30	20	AEG - B&D - Bosch - Festo - Haffner - Holz Her - Mafell - Peugeot - Scheer - Skil - Stayer	9500	756.42	1	756424
230	30	34		9500	756.44	1	756448
250	30	24	Elektra Beckum - Elu - Mafell - Metabo	8000	756.48	1	756486
250	30	48		8000	756.50	1	756509
250	30	60		8000	756.52	1	756523
300	30	72	Elektra Beckum - Elu	4000	756.56	1	756561
300	30	96		4000	756.58	1	756585
350	30	84	Festo	4000	756.60	1	756608
350	30	108		4000	756.62	1	756622