

HSS - DIN 338 HIGH SPEED STEEL TWIST DRILL

Hexagonal shank 1/4"

465.02	ø 2 mm	10	465029
465.03	ø 3 mm	10	465036
465.04	ø 4 mm	10	465043
465.05	ø 5 mm	10	465050

**HSS - DIN 338 HIGH SPEED STEEL TWIST DRILL**

ø mm	PG BLISTER		BULK		q.ty
	ref.	EAN13 8011017	ref.	EAN13 8011017	
1	10.010 - 2 drills	100104	17.010	170107	10
1,5	10.015 - 2 drills	100159	17.015	170152	10
2	10.020 - 2 drills	100203	17.020	170206	10
2,5	10.025 - 2 drills	100258	17.025	170251	10
3	10.030 - 2 drills	100302	17.030	170305	10
3,5	10.035 - 2 drills	100357	17.035	170350	10
4	10.040 - 2 drills	100401	17.040	170404	10
4,5	10.045	100456	17.045	170459	10
5	10.050	100500	17.050	170503	10
5,5	10.055	100555	17.055	170558	10
6	10.060	100609	17.060	170602	10
6,5	10.065	100654	17.065	170657	10
7	10.070	100708	17.070	170701	10
7,5	10.075	100753	17.075	170756	10
8	10.080	100807	17.080	170800	10
8,5	10.085	100852	17.085	170855	10
9	10.090	100906	17.090	170909	10
9,5	10.095	100951	17.095	170954	10
10	10.100	101002	17.100	171005	10
10,5	10.105	101057	17.105	171050	10
11	10.110	101101	17.110	171104	10
11,5	10.115	101156	17.115	171159	10
12	10.120	101200	17.120	171203	10
12,5	10.125	101255	17.125	171258	10
13	10.130	101309	17.130	171302	10
13,5			17.135	171357	5
14			17.140	171401	5
14,5			17.145	171456	5
15			17.150	171500	5
15,5			17.155	171555	5
16			17.160	171609	5

