



PC case accessories

Model: **AK-CA-37**



Product code	AK-CA-37
Product type	PC case accessories
Format	3.5"
USB 2.0 ports on the front panel	1 pc
Cable length	30 cm
The cable plug #1	USB IDE 10-pin
Material	ABS + metal
Product color	Black
Temperature	5 - 50 °C
Package	EcoBox
Product size (L x W x H)	124 x 100 x 25 mm
Package size (L x W x H)	175 x 110 x 30 mm
Net weight	73.2 g
Gross weight	109.8 g
CE compatibility	Yes
FCC compatibility	Yes
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720132734
Warranty	24 months



Description

Akyga® **AK-CA-37** internal memory card reader intended to install in **external 3.5" drive bay** (Floppy Disc Drive). There is also additional **USB 2.0** port on a front panel that allows data transfer with speed **up to 480 Mb/s**.

Supported card types:

- MultimediaCard: MMCType I, MMCType II, Ultra MMC, RS-MMC, C4.0, C Plus, C mobile, C micro, Dvrs MMC HS MMC;
- Secure Digital Card: SD, MiniSD, UltraSD, Kingmax SD, Extreme SD, SD Ultimate, SD Elite pro, SD HC, micro SD, microSDHC;
- Memory Stick: MS, MS-pro, MS-Duo, MS-pro-Duo, MS-MG-pro, MS-MG-Duo, MS-MG-pro-Duo, Ultra MS, MS select function card, Extreme MS, Micro Drive, XD, T-flash, C-flash;
- Compact Flash (works with 16 GB cards): CF I, CF II, Extreme III CF, Ultra II CF, CF SA.