



USB Cable

Model: **AK-USB-37**



Product code	AK-USB-37
Product type	USB Cable
Maximum power	100 W (20 V / 5 A)
Cable length	1.0 m
The cable plug #1	USB Male connector type C
The cable plug #2	USB Male connector type C
Data transmission	480 Mbps
Plated plugs	Yes - nickel plated
Product color	Blue
Package	UniBag
Product size (L x W x H)	80 x 90 x 10 mm
Package size (L x W x H)	150 x 105 x 11 mm
Net weight	35 g
Gross weight	38 g
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720137517
Warranty	24 months



Description

The Akyga® AK-USB-37 USB cable has been created for **fast charging** of devices with a maximum power of **100 watts**. It has been terminated on both sides with USB Type C connectors. This makes it compatible with modern devices such as smartphones, tablets and laptops. Both plugs of the USB-C cable are equipped with **E-Mark technology**. It is responsible for ensuring that the energy transmitted through the **USB-C cord** is safe for the connected device. Thus, it is ideal for chargers with Power Delivery technology. With this, you can easily charge any equipment with a single cable. This not only saves space on your desk, but also eliminates the tangle of cables in your travel bag. What's more, **the 1 m long USB-C cable** is characterised by its high resistance to abrasion. It owes this to the robust **nylon braid**, which directly extends the life of the USB-C cable.

The cable is compatible with Power Delivery (PD), Quick Charge (QC), as well as Samsung (AFC), Huawei (FCP/SCP), or Apple (2.4 A) chargers.