



USB Cable
Model: **AK-USB-40**



Product code	AK-USB-40
Product type	USB Cable
Maximum power	60 W (20 V / 3 A)
Cable length	1.0 m
The cable plug #1	USB Male connector type C
The cable plug #2	USB Male connector type C
Data transmission	Yes
Plated plugs	Yes - nickel plated
Product color	White
Package	UniBag
Product size (L x W x H)	110 x 70 x 10 mm
Package size (L x W x H)	150 x 105 x 11 mm
Net weight	26 g
Gross weight	29 g
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720137548
Warranty	24 months



Description

The Akyga® **AK-USB-40 USB-C cable** is a practical accessory that has been fitted with **USB Type C terminals** on both sides. This cable is used for charging small electronic devices such as mobile phones, portable speakers or tablets. To do this, connect it to a charger or computer. The long **1 m cable** ensures convenient use even in hard-to-reach places. In addition, it allows safe and extremely efficient charging of electronic equipment with **60 W** and a maximum current of **3 A**. Thus, it is compatible with chargers with Power Delivery, Quick Charge and other fast charging standards.

The Akyga® AK-USB-40 cable works with devices that have a USB-C input, including the iPad Pro or MacBook Pro. The **symmetrical tip**, which allows even easier charging of devices. Thanks to the axial design of the USB-C connector, it doesn't matter which way you plug the cable into your charger or mobile phone. This is a huge convenience if you can't see the device input. The accessory's light weight and size make it ideal for travel, the office or at home. High-quality components guarantee a long service life and trouble-free operation, as well as the safety of your devices.