



USB Cable

Model: **AK-USB-41**



Product code	AK-USB-41
Product type	USB Cable
Maximum power	60 W (20 V / 3 A)
Cable length	1.8 m
The cable plug #1	USB Male connector type C
The cable plug #2	USB Male connector type C
Data transmission	Yes
Plated plugs	Yes - nickel plated
Product color	White
Package	UniBag
Product size (L x W x H)	135 x 85 x 15 mm
Package size (L x W x H)	180 x 130 x 16 mm
Net weight	43 g
Gross weight	48 g
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720137555
Warranty	24 months



Description

Akyga® AK-USB-41 is a high-quality **USB-C cable** for charging mobile devices. It has been terminated on both sides with symmetrical **USB type C** connectors. Thanks to this, it fits most modern devices such as mobile phones, tablets or even laptops. What's more, the cable is designed to charge equipment with a maximum power of **60 W**. Therefore, it can easily be connected to powerful chargers with a fast-charging function. It is compatible with both Power Delivery (PD) and Quick Charge (QC) standards, as well as Samsung AFC, Huawei FCP/SCP or Apple 2.4 A. Furthermore, the cable can be used not only **to charge devices**, but also **to transfer data** between them.