



USB Cable

Model: **AK-USB-44**



Product code	AK-USB-44
Product type	USB Cable
Maximum power	15 W (5 V / 3 A)
Cable length	1.0 m
The cable plug #1	USB Male connector type micro-B 3.0
The cable plug #2	USB Male connector type C 3.1
Data transmission	5 Gb/s
Plated plugs	Yes - nickel plated
Material	Copper
Product color	Black
Package	UniBag
Product size (L x W x H)	110 x 90 x 11 mm
Package size (L x W x H)	180 x 130 x 13 mm
Net weight	28.2 g
Gross weight	33.6 g
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720137715
Warranty	24 months



Description

The Akyga AK-USB-44 is a USB 3.0 **external drive cable**. At one end it has a **micro USB B connector**, found on older models of external drives. On the other is a **USB-C connector**, which is commonly used in mobile devices. Thanks to this, the cable makes it possible to connect an SSD or HDD to a modern computer as well as a smartphone or tablet. It is a convenient solution that allows **fast data transmission of 5 Gbps** and **charging with up to 15 W**.