

AREA 10 CONNECT

10000 lumen 360° work light for 18V battery packs



ORIGINAL
SCANGRIP



SINCE 1906

AREA 10 CONNECT provides a diffused and uniform light up to 10,000 lumen which is ideal for the professional user who requires powerful and efficient illumination of the entire work area carrying out any kind of repair, paint or construction work.


The compact design with a carrying handle makes it extremely handy and easy to move around. Change between 360° and 180° illumination according to the work task. The built-in dimmer function enables you to adjust the light output into five different levels.

AREA 10 CONNECT is compatible with METABO / CAS battery system 12V 4.0 Ah - 18V 5.2 Ah and all other 18V battery packs from leading power tool brands by using the SCANGRIP CONNECTOR. In addition, the POWER SUPPLY can be used for direct power providing unlimited availability to light. AREA 10 CONNECT also has an internal back-up battery securing 50 extra minutes at 1000 lumen.

With the integrated BLUETOOTH light control it is possible to turn on/off the work light and adjust the light output through a mobile device, saving you time from manual operation and increases work efficiency on a daily basis.

Due to the compact and low weight design, AREA 10 CONNECT is portable and easy to carry around. It is also supplied with a hook for flexible positioning and can be mounted directly on the SCANGRIP TRIPOD. Dust and waterproof, IP65, and supplied with a built-in power bank with USB outlet to charge mobile devices.

Bluetooth
Light control app



Change between
360° and 180°
illumination



NEW

BATTERY, CHARGER, CONNECTORS AND POWER SUPPLY ARE SOLD SEPARATELY

SCANGRIP CONNECTORS for 18V battery packs



BERNER - 03.6155C
BOSCH - 03.6140C
BOSCH GREEN - 03.6141C
DEWALT - 03.6142C
EINHELL - 03.6143C
FEIN - 03.6144C
FESTOOL - 03.6153C
FLEX - 03.6145C
HAZET - 03.6146C
HIKOKI - 03.6147C
INGERSOLL - 03.6152C
MAKITA - 03.6148C
MILWAUKEE - 03.6149C
RIDGID - 03.6154C
SNAP-ON - 03.6151C
WÜRTH - 03.6150C

Accessories



POWER SUPPLY
03.6123C



CAS BATTERY
12V 4.0 Ah
03.6120



CAS BATTERY
18V 5.2 Ah
03.6121



CAS CHARGER
03.6122

DESIGNED BY
SCANGRIP
IN DENMARK

TECHNICAL SPECIFICATIONS

240 LEDs
189 lm/W
300-3000 lux@0.5m
360°: 10000 lm @ 100% / 7500 lm @ 75% / 5000 lm @ 50% / 2500 lm @ 25% / 1000 lm @ 10%
180°: 5000 lm @ 100% / 3750 lm @ 75% / 2500 lm @ 50% / 1250 lm @ 25% / 500 lm @ 10%
Compatible with METABO/CAS battery system 12V 4.0 Ah - 18V 5.2 Ah and all other 18V battery packs by using the SCANGRIP CONNECTOR
Operating time: 0.5-10h @ 12V 4.0 Ah battery, 1-22h @ 18V 5.2 Ah battery, Backup: 50min @ 1000 lm
-10° to +40°C
IK07
IP65, IP54 with battery cover
3.7 kg
395x200x212 mm

JUST CONNECT

Add the connector matching your battery pack



AREA 10 CONNECT

Item no. 03.6103C