

MUSG-001-R

Gaming mouse, USB, red

DESIGNED FOR TRUE GAMERS

- Optimal comfort for intense and extended gameplay
- 2400 DPI 3 x more precision than standard mice
- Non-slip rubberized ergonomic design



Features

- 6-button 2400 DPI gaming mouse
- Quick DPI button (600-2400 dpi)
- Illuminated scroll wheel, logo and side accents
- Comfortable ergonomic design
- Rubber coated top for more grip and control
- Practical tangle free nylon mesh cable

Specifications

Interface: USB 2.0
Optical resolutions: 600, 800, 1200, 1600, 2400 DPI
Ambidextrous: yes
Button life time: 5 million clicks
Cable: nylon tangle free
Cable length: 1.3 m
Dimensions: 130 x 72 x 41 mm

Packaging

Q'ty in crtn, pcs	40
Crtn volume, CUM	0.077
Crtn weight, kgs	8.99
Individual package size LxWxH:	205x145x55 mm
Carton size LxWxH:	580x430x310 mm
Country of origin	CN
Barcode	8716309081900
Customs code	8522900090

System requirements

Windows XP/Vista/7/8
Free USB port

Certificates

