

MUSG-05

Programmable gaming mouse

DESIGNED FOR TRUE GAMERS

- Supports Macro programming
- Optimal comfort for intense and extended gameplay
- 4000 DPI much more precision than standard mice
- Ergonomic design suitable for long comfortable gaming sessions



Features

- 7-button 4000 DPI programmable gaming mouse
- Quick DPI button (600-4000 dpi)
- Programmable macro buttons for advanced gaming experience
- 7-color breathing RGB light effect
- Comfortable ergonomic design
- Including easy to use macro programming software

Packaging

Q'ty in crtn, pcs	40
Crtn volume, CUM	0.101568
Crtn weight, kgs	12.52
Individual package size LxWxH:	220x162x60 mm
Carton size LxWxH:	640x345x460 mm
Country of origin	CN
Barcode	8716309097475
Customs code	8522900090

Package contents

Mouse
User manual
Software CD

Specifications

Interface: USB 2.0
 Sensor: Avago A3050 gaming sensor
 Optical resolutions: 600, 800, 1000, 1200, 1800, 2000, 2400, 4000 DPI
 Report rate: 1000 Hz
 Acceleration: 16G
 Button life time: 10 million clicks
 Power consumption: 5 V DC, max. 100 mA
 Material: ABS + metal
 Cable length: 1.5 m
 Dimensions: 128 x 80 x 45 mm

System requirements

Windows XP/Vista/7/8/8.1/10
 Free USB port

Certificates

