

MUS-ERGO-01

Ergonomic 6-button wired optical mouse, black

COMFORT AND PRECISION

- Ergonomic design minimizes strain on the arm, wrist and hand
- No mouse pad required



Features

- 6-button wired optical mouse (right handed)
- Ergonomic vertical hand position prevents fatigue and minimizes wrist problems
- CPI button for quick resolution changes (1200-3200 DPI)
- Next/Previous buttons for faster Internet browsing

Specifications

Interface: USB
Optical resolution: 1200, 1600, 2400, 3200 DPI selectable by the button
Ambidextrous: No, for right handed use only
Power consumption: 1.5 V DC, up to 15 mA
Mouse: dimensions 95 x 65 x 36 mm, net weight 98 g

Packaging

Q'ty in crtn, pcs	30
Crtn volume, CUM	0.099290625
Crtn weight, kgs	7.48
Individual package size LxWxH:	165x75x225 mm
Carton size LxWxH:	525x445x425 mm
Country of origin	CN
Barcode	8716309104890
Customs code	8522900090

Package contents

Mouse

System requirements

Windows 7/8/10
Free USB port

Certificates

