

MUS-GU-02

USB G-laser wired mouse

- Compact & lightweight design
- 2400 dpi G-Laser technology for more precision
- Plug & Play no drivers required



Features

- 6-button G-laser wired mouse with scroll wheel
- Advanced G-laser sensor for perfect pointer precision
- DPI button for quick resolution changes (800 2400 DPI)
- Next/Previous buttons for faster Internet browsing
- Works on most surfaces

Specifications

Interface: USB
Resolution: 800, 1200, 1600, 2400 DPI selectable by the button
Tracking speed: 50-250 mm/s
Dimensions: 118 x 66 x 38 mm
Cable length: 1.8 m

Packaging

Q'ty in crtn, pcs	60
Crtn volume, CUM	0.073
Crtn weight, kgs	9.2
Individual package size LxWxH:	190x135x50 mm
Carton size LxWxH:	600x420x290 mm
Country of origin	CN
Barcode	8716309117692
Customs code	8522900090

System requirements

Windows 7/8/10
Free USB port

Certificates

