

GHS-05-O

Gaming headset with volume control, orange-black, 3.5 mm

FOR TRUE GAMERS

- Clear high quality sound
- Stylish design, comfortable fit
- Perfect for PlayStation 4, Xbox or PC



Features

- Gaming headset with rotating microphone boom
- Adjustable headband and comfortable large ear cushions
- Suitable for use with e.g. PlayStation 4, Xbox One or PC
- Practical in-line volume control

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.081
Crtn weight, kgs	7.16
Individual package size LxWxH:	185x85x200 mm
Carton size LxWxH:	460x430x410 mm
Country of origin	CN
Barcode	8716309117159
Customs code	8518300090

Specifications

Interface: CTIA 4-pin 3.5 mm plug
Driver unit: 40 mm
Impedance: 32 Ohms $\pm 10\%$
Frequency response: 20 20000Hz
Sensitivity: 102 dB ± 3 dB S.P.L at 1 kHz
Max. input power: 100 mW
Microphone: electret, omni-directional, 6 mm, 2.2 KOhm impedance

Frequency response: 20 16000 Hz
Sensitivity: -40 dB ± 3 dB
Connectors: stereo 3.5 mm + mic plug (CTIA 4-pin)
Cord length: 2 m

System requirements

Device equipped with 3.5 mm combo CTIA 4-pin audio socket

Certificates

