

MHS-001

Stereo headset, glossy black

MUSIC & MORE

- Clear and powerful sound
- Comfortable to wear
- Perfect for music, gaming and online chats



Features

- Stereo headset with rotating microphone boom
- Practical in-line control for volume
- Large comfortable ear cushions
- Comfortable, adjustable headband

Specifications

Sensitivity (at 1KHz) : 105 +/-3 dB
Impedance : 32 Ohm +/-15%
Speakers: 40 mm diameter, 16u mylar
Frequency response: 20 20000 Hz
Input power: up to 100 mW max
Distortions: < 3 % at 1KHz 40mW
Microphone: condenser omni-directional; sensitivity:-58 ± 3 dB(0 dB=1V/uBar at 1KHz), -38dB (0 dB=1V/Pa at 1KHz), 30 16000 Hz
Net weight: 0.2 kg

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.063
Crtn weight, kgs	6.33
Individual package size LxWxH:	192x192x75 mm
Carton size LxWxH:	410x395x392 mm
Country of origin	CN
Barcode	8716309079495
Customs code	8518300090

System requirements

3.5 mm stereo and microphone input sockets

Certificates

