

MHS-03-WTRD

Stereo headset, white color with red ring

MUSIC & MORE

- Clear and powerful sound
- Comfortable to wear
- Perfect for music, gaming and online chats



Features

- Stereo headset with rotating microphone boom
- Practical in-line volume control
- Large comfortable ear cushions
- Comfortable, adjustable headband
- 3.5 mm combo stereo + microphone jack for mobile phones

Specifications

Connector: 3.5 mm 4-pin combo-jack, stereo + microphone
Sensitivity (at 1KHz) : 105 +/-3 dB
Impedance : 32 Ohm +/-15%
Speakers: 40 mm diameter, 16u mylar
Frequency response: 20 20000 Hz
Input power: up to 100 mW max
Distortions: < 3 % at 1KHz 40mW
Microphone: condenser omni-directional; sensitivity:-58 ± 3 dB(0 dB=1V/uBar at 1KHz), -38dB (0 dB=1V/Pa at 1KHz), 30 16000 Hz

Net weight: 0.2 kg

Packaging

Q'ty in crtn, pcs	12
Crtn volume, CUM	0.04284
Crtn weight, kgs	4.18
Individual package size LxWxH:	210x75x240 mm
Carton size LxWxH:	500x204x420 mm
Country of origin	CN
Barcode	8716309113670
Customs code	8518300090

System requirements

3.5 mm 4-pin stereo and microphone input combo-socket

Package contents

Headset w/ mic

Certificates

