

MIC-DU-02

USB desktop microphone, black

- Flexible neck to easily position the microphone
- Perfect for online communications



Features

- USB desktop microphone
- Flexible neck

Specifications

Interface: USB 2.0
Microphone: omni-directional condenser type
Sensitivity: 67 dBV/pBar (-47 dBV/Pascal) +/-4 dB
Frequency response: 100 16000 Hz
Dimensions: 55 x 55 x 130 mm

Packaging

Q'ty in crtn, pcs	20
Crtn volume, CUM	0.052
Crtn weight, kgs	3
Individual package size LxWxH:	1x1x11 mm
Carton size LxWxH:	500x350x300 mm
Country of origin	CN
Barcode	8716309117395
Customs code	8518300090

System requirements

A free USB-port
Windows 7/8/10

Certificates

