

650 VA "Basic 650" UPS, Shuko output sockets, black

EG-UPS-B650

ULTIMATE DEFENCE

- Provides backup power prevents data loss
- Protects your sensitive and valuable equipment
- Compact and reliable ideal for home and small office use



Features

- Uninterruptable 650 VA power supply for PC's
- Automatic output voltage regulation (AVR)
- LED status indication
- Short circuit protection
- Surge, spike and lightning protection
- Audible and visual alarms
- Overcharge and overdischarge protection

Packaging

Q'ty in crtn, pcs	4
Crtn volume, CUM	0.043792
Crtn weight, kgs	19.2
Individual package size LxWxH:	338x147x210 mm
Carton size LxWxH:	560x340x230 mm
Country of origin	CN
Barcode	8716309087087
Customs code	8504408490

Package contents

UPS
User manual

Specifications

UPS type: line interactive
 Input: AC 220V±28%, 50Hz/60Hz ±10%
 Output: AC 220V±10%, 50Hz/60Hz ±0.5% (on battery)
 Switching time: no more than 10 ms
 Backup time: up to .20 mins (depends on the load)
 Battery: 151 x 65 x 95 mm, sealed lead-acid 12V/7Ah x 1 pc
 Charge time: up to 12 hours
 Sockets: 2 x Schuko output (CEE 7/4)
 Operating conditions: 0°C~40°C, at humidity 10~90%RH non condensing
 Power: 650 VA (390 W)

System requirements

In order to work correctly, the connected load should be at least 5% of the maximum capacity of the UPS. For example, a 700 W UPS needs at least a connected load of 35 W to work.

Certificates

