

NIC-GX1

Gigabit Ethernet PCI-Express card, Realtek chipset

GET MORE FROM YOUR PC

- 1000 Mbps data transfer speed
- Perfect upgrade for your desktop
- Easy plug&play installation



Features

- Gigabit PCI-Express LAN add-on card
- Single STP RJ45 port for either 1000 Mbps, 100 Mbps or 10 Mbps network speeds
- Supports speed auto-negotiation, pair swap/polarity/skew correction, crossover detection
- Automatic IRQ and I/O address setup
- Supports Microsoft Windows, MAC OS, Unix/Linux, Novell

Packaging

Q'ty in crtn, pcs	60
Crtn volume, CUM	0.05544
Crtn weight, kgs	7
Individual package size LxWxH:	160x27x145 mm
Carton size LxWxH:	480x350x330 mm
Country of origin	CN
Barcode	8716309052399
Customs code	8522900090

Package contents

Addon card
Low profile bracket

Specifications

Supports PCI-Express bus v.1.0a
Compliant with IEEE802.3ab 1000BASE-T Gigabit Ethernet standard, IEEE802.3u Fast Ethernet standard, IEEE 802.3
Supports IEEE 802.1Q VLAN tagging
Supports IEEE802.1P Layer 2 Priority Encoding
Supports Full Duplex flow control (IEEE 802.3x), power saving, Wake-on-LAN, remote wake-up, PCI Message Signaled Interrupt (MSI)

Chipset: RTL8111C

Dimensions: 120 x 80 x 20 mm, x1 slot

System requirements

Free PCI-Express x1 (or wider) slot
Windows 98/Me/NT/2000/XP/Vista/7/8 (32 & 64 bit), MAC OS v.10.4 or higher (on Intel-based MAC computer), Unix/Linux, Netware

Certificates

