



Note:

L(Length)	T(Tolerance)	Part number	Color
1000	20	SN318-3/14/1.0WH	WHT
1000	20	SN318-3/14/1.0GY	GRY
1500	50	SN318-3/14/1.5WH	WHT
1500	50	SN318-3/14/1.5GY	GRY
1800	50	SN318-3/14/1.8WH	WHT
1800	50	SN318-3/14/1.8GY	GRY
2000	50	SN318-3/14/2.0WH	WHT
2000	50	SN318-3/14/2.0GY	GRY
3000	50	SN318-3/14/3.0WH	WHT
3000	50	SN318-3/14/3.0GY	GRY
5000	50	SN318-3/14/5.0WH	WHT
5000	50	SN318-3/14/5.0GY	GRY



NOTE :

1. PLUG : LT-202 AMERICAN TYPE
2. CONNECTOR : LT-549 IEC 60320 C19
3. Strain relief : NA
4. CORD : SJT 3X14AWG 60D
5. APPROVALS : UL , C-UL
6. CUSTOMER : TME
7. Supplier for flexible cord : RHYTHM, STANDARD, WU LI, I-SHENG
8. P/N : Above Note Chart

修改履歷

6		
5		
4		
3		
2		
1	新增	22/09/28
REV.	DESCRIPTION	DATE

DRAWER	Aaron	DATE	22/09/28	TITLE	LT-202+549
APPROVE		REV.	1	Dr.No.	1110961
		比例		TOL.	±5mm
				ALL DIMENSIONS IN mm	

※Customer drawing number : NA



LIAN DUNG
ELECTRIC WIRE MATERIAL CO.,LTD.
聯東電線材料股份有限公司